



Cummins Warranty Quick Reference Guide

U.S. AND CANADA



Cummins Engines (Base Warranty)

Automotive Engines	Months	Mileage/Km/Hrs
4B/ISB4 Series	24	50,000/80,468
2017+ EPA B/B6.7/ISB	36	Unlimited
B/B Gas Plus/B LPG Plus/ISB ISV/V5.0	24	Unlimited
ISC/ISL/ISL G/C Gas Plus	24	250,000/402,336/6,250
L10/M11/ISM/N14/ISX/ Signature*	24	250,000/402,336/6,250
2010 EPA & 2013 EPA ISX11.9 (ISX12) / ISX15	24	250,000/402,336/6,250
2017+ EPA X12 / X15	24	250,000/402,336/6,250
Fire Truck/Crash Truck	60	100,000/160,935
Worldwide All Bus Categories - All Engines (except U.S. and Canada Diesel Powered School Buses)	24	Unlimited
U.S./Canada School Bus	60	100,000/160,935
RV - ISB AD	36	75,000/120,701
All Other RV Engines	60	100,000/160,935

* Injectors are covered for 2 years/125,000 miles/201,169 km/3,125 hours.

Industrial Engines	Months	Hours
All Industrial Engines**	24	2,000

**If the 2,000-hour limit is exceeded during the first year, coverage continues until the end of the first year.

EXTENDED MAJOR COMPONENTS PARTS WARRANTY

Coverage*	Automotive Engines	What is Covered
5 years / 500,000 miles / 804,676 kilometers	L10/M11/ISM/N14/ISX/ Signature automotive engines	Registered parts, labor, other claimables
3 years / 10,000 hours	Industrial engines	Registered parts only: Cylinder block, Connecting rod, Crankshaft, Camshaft
3 years / 10,800 hours / 300,000 miles / 482,805 km	Coach / Transit / Shuttle / School Bus	

Genuine Cummins New Parts

Components	Months	Mileage/Km/Hrs
Centinel™		
- Automotive	24	250,000/402,336/3,600
- Industrial	12	Unlimited
N Series/L10/M11/ISM/ISX/HD*	12	100,000/160,935/3,600
A, B/B Gas Plus/B Gas International/ B LPG Plus/ISB5.9 G/ISB/QSB, C/C Gas Plus/ISC/ QSC, ISF, ISL/ISL G/QSL/MR* - engines up to 10L	12	100,000/160,935/3,600
K19/QSK19/QSK23/QSK45/ QSK60/QSK78/HHP*	12	Unlimited
Cummins Cylinder Kits:		
- All 1991 and Newer N14 TriTech® Plus Cylinder Kits	36	300,000/482,804/10,800
- Single Ni TriTech Plus	24	200,000/321,869/7,200
- Dual Ni TriTech	36	300,000/482,804

*Refer to service bulletin 6649234 on QuickServe for definition of MR, HD, and HHP.

- Variable geometry turbochargers and electronic actuators in North American on-highway applications are not eligible for over-the-counter exchanges if the parts are installed after October 1, 2018.
- Diesel Oxidation Catalyst (DOC), Diesel Particulate Filter (DPF), Selective Catalyst Reduction (SCR) catalyst, and Electronic Control Modules (ECM) in North American on-highway applications are not eligible for over-the-counter exchanges if the parts are installed after January 1, 2020.

EXTENDED MAJOR COMPONENTS PARTS WARRANTY*

Coverage**	What is Covered?
3 years, 300,000 miles, 482,804 kilometers, or 108,800 hours	Parts***, Cylinder Block, Camshaft****, Crankshaft, Connecting Rods

* Only applies to HD and HHP New Parts.

** Whichever one occurs first, after expiration of new parts base warranty.

*** Bushing and bearing failures are NOT covered.

**** The Extended Major Components Warranty for camshafts applies only to flangeless NT camshafts when installed with crowned cam follower rollers.

Cummins ReCon[®] Engines/Blocks

Automotive Engines	Months	Mileage/Km
B3.9	24	50,000/80,468
B5.9/ISB/B Gas Plus/B LPG Plus	24	100,000/160,935
ISC/C8.3/ISL/C Gas Plus/ISL G/L Gas Plus - Up to 225 hp	24	Unlimited
ISC/C8.3/ISL/C Gas Plus/ISL G/L Gas Plus - Up to 226 hp and Over	24	100,000/160,935
L10/M11/ISM/N/N14	12	100,000/160,935
ISM/ISC/ISL/ISB Transit (excluding hybrid)	24	Unlimited
ISX	24	200,000/321,869
4B/6B/ISB/6C/ISC/ISL Long Blocks	12	50,000/80,468
L10/M11/ISM/N14/ISX Long Blocks	12	100,000/160,935
4B/6B/ISB/6C/ISC/ISL Short/Service Blocks	6	Unlimited
L10/M11/ISM/N14/ISX Short/Service Blocks	12	100,000/160,935

Industrial	Months	Hours
All Industrial Engines*	24	2,000
All Marine Engines*	24	2,000
4B/6B/6C/L10/M11/N14/K19/QSB/QSC/QSL/QSM/ QSX/QSK19 Long Blocks	12	1,000
6B/6C/N14/K19 Oil and Gas Long Blocks	12	Unlimited
4B/6B/6C/QSB/QSC/QSL Short/Service Blocks	6	Unlimited
L10/M11/N14/K19/QSM/ QSX/QSK19 Short/Service Blocks	6	Unlimited

* If the 2,000-hour limit is exceeded during the first year, coverage continues until the end of the first year.

Cummins ReCon Parts

Components	Months	Mileage/ Km/Hrs	Labor	Travel	Other Claimables
ReCon Electrics	12	Unlimited	Y	Y*	Y
Components-Engines up to 18L (except fuel pumps, injectors and electrics)**	12	100,000 / 160,935 / 3,600	Y	Y*	Y
ReCon High-Volume Water Pumps***	24	200,000 / 321,870 / 7,200	Y	Y*	Y
ReCon Premium Gold Cylinder Head****	24	200,000 / 321,870 / 7,200	Y	Y*	Y
Injectors and Fuel Pumps - engines up to 18L	12	Unlimited	Y	Y*	Y
Heavy-Duty ReCon PX Injectors - L10/M11/ISM N14/ ISX Pre EPA 2010	24	125,000 / 201,168 / 3,600	Y	Y*	Y
MidRange ReCon Injectors	12	Unlimited	Y	Y*	N
All Other HD Components Except Electrics	12	100,000 / 160,935 / 3,600	Y	Y*	Y
CELECT™ & HPIRX Injectors for N.A. and Mexico	12	Unlimited	N	N	N
ReCon RX Injectors for N.A. and Mexico	12	100,000 / 160,935 / 3,600	Y	N	N
HHP ReCon Components	12	Unlimited	Includes covered parts, labor and travel		
HHP Engines Extended Major Components Parts Warranty	36	10,800 hrs			
ReCon "XX" Products	6	Unlimited			
ReCon RX DPF Not Sold in CA	12	100,000 / 160,935 / 3,600	Y	Y	Y

* When parts are installed in a non-automotive engine, Cummins will pay reasonable travel expenses to the engine site, or to a repair dock in the case of a Cummins Marine engine.

** Variable geometry turbochargers and electronic actuators in North American on-highway applications are not eligible for over-the-counter exchanges if the parts are installed after October 1, 2018.

Diesel Oxidation Catalyst (DOC), Diesel Particulate Filter (DPF), Selective Catalyst Reduction (SCR) catalyst, and Electronic Control Modules (ECM) in North American on-highway applications are not eligible for over-the-counter exchanges if the parts are installed after January 1, 2020.

*** Applies only to part numbers: AR4518RX, AR45184-1RX, AR45090RX, AR45090-1RX, 3045943RX, 3801708RX, 3801715RX, 3801788RX, 3803138RX, 3803605RX.

**** Applies only to part numbers: 3652600RX, 3652807RX, 3652808RX, 3675504RX, 3675505RX, 3675506RX.

Cummins Service Tools

Tools	Months	Coverage
QuickCheck™ 5600	12	Parts
INLINE™ 6	12	Parts
INLINE™ 7	Manufacturer's Warranty Applies	
INLINE MINI™	Manufacturer's Warranty Applies	
Genuine Tools	Lifetime	Repair or Replace
Electrical Products, Instrumentation, Gauges, Motors and Consumables	12	Repair or Replace
Non-Genuine Tools	Manufacturer's Warranty Applies	

*(Refer to Page i-3 of the Cummins Service Products Catalog, Bulletin 3377710-03, for details.)

Note: The warranty terms described within this card are correct at time of printing, subject to change without notice, and apply only to Genuine Cummins products purchased from an authorized Cummins distributor/dealer. Exceptions may apply. See individual warranty certificates for complete warranty coverage. Contact your local Cummins distributor or dealer for more details. The "Warranty Administration Manual" is published on QuickServe as bulletin: 4021290.



Cummins Inc.
Box 3005
Columbus, IN 47202-3005
U.S.A.

cummins.com

Bulletin 4081630 Produced in U.S.A. 8/25
©2025 Cummins Inc.